

TexWipe



Tuch BlueWipe #TX512

pure¹¹-Nr.: 1106073, Marke: TexWipe

Eigenschaften

- Marke: TexWipe
- Flächengewicht in g/m²: 70 g/m²
- Material: Polyester/Zellulose
- Lieferform in Verpackung: gefaltet
- Verpackungsform: Beutel
- Anzahl in kleinster Unterverpackung: 50
- Autoklavierbar
- Kantenverarbeitung: Kalt geschnitten
- Gebrauch: Einweg
- Hydroverfestigt
- Polyester/PES: 45 %
- Zellulose: 55 %
- Flächengewicht in g/m²: 70 g/m²

Empfohlene Reinraumklassen

ISO 5|6|7|8|9

GMP C|D



Material

- Polyester/Zellulose

Verpackung

- 500STK

Produktvarianten

pure¹¹-Nr.: 1106073, Tuch BlueWipe #TX512

Größe: 31 x 31 cm (12 x 12"); Farbe: Blau / VE: 500STK

TECHNICAL DATA SHEET

Performance Characteristics

Property	Typical Value	Test Method*
Particles and Fibers LPC: $\geq 0.5 \mu\text{m}$ Fibers: $> 100 \mu\text{m}$	78 x 10 ⁶ particles/m ² 140,000 fibers/m ²	1, TM22 2, TM22
Nonvolatile Residue IPA extractant DIW extractant	0.03 g/m ² 0.07 g/m ²	1, TM1 1, TM1
Ions Sodium Potassium Chloride	10 ppm 2 ppm 13 ppm	1, TM18 1, TM18 1, TM18

Physical Characteristics

Property	Typical Value	Test Method*
Absorbency Sorptive capacity Sorptive rate	280 mL/m ² 4 seconds	1, TM20 1, TM20
Basis Weight	70 g/m ²	1, TM20

***Test Methods**

- 1 – “Evaluating Wiping Materials Used in Cleanroom and Other Controlled Environments,” IEST-RP-CC004.3, Institute for Environmental Sciences and Technology, Rolling Meadows, IL, 2004; www.iest.org.
- 2 – E2090-12, “Standard Test Method for Size-Differentiated Counting of Particles and Fibers Released from Cleanroom Wipers Using Optical and Scanning Electron Microscopy,” ASTM International, West Conshohocken, PA, 2012; www.astm.org.
- TM – Refers to Texwipe Test Method – available upon request. Contact Texwipe Customer Service at www.texwipe.com or info@texwipe.com for a copy.

Note: The data in this table represent typical analyses.

Texwipe holds ISO 9001 and ISO 14001 registrations.

All Texwipe products conform to GHS classification for labeling (where applicable).

Shipping classification based on weight of inner package.

BlueWipe[®]

Dry Wipers

TECHNICAL DATA SHEET



BlueWipe®
45% polyester / 55% cellulose



Made in USA

Products

Number	Description	Sterile	Packaging	Case
<i>Dry Wipers – BlueWipe®</i>				
TX512	12" x 12" (31 cm x 31 cm) dry		50 wipers/bag	10 bags

TECHNICAL DATA SHEET

Description

BlueWipe® is made from 45% polyester / 55% cellulose nonwoven colorfast material with a cut edge, cleanroom manufactured.

Applications

- Wiping and cleaning surfaces, equipment and parts.
- Spill control.
- Applying and removing lubricants, adhesives, residues and other solutions including disinfectants.
- Cleaning with solvents such as isopropyl alcohol (IPA), ethanol, acetone, and degreasers.
- Lining trays for holding, protecting, drying and storing of parts, equipment and devices.

Industries

Aerospace	Animal Laboratory	Biologics
Cleanroom Design/Build	Compounding Pharmacies	Data Storage
Facilities Maintenance	Industrial	Laboratory
Medical Device	Microelectronics	Pharmaceutical
Printing/Graphics	Semiconductor	USP <797> / USP <800>

Features & Benefits

- Constructed from 45% polyester / 55% cellulose nonwoven creating a durable wiper ideal for spill control, cleaning, and solution application.
- Excellent chemical resistance for compatibility with a variety of solutions.
- Packaged in a C-fold design for easy access and removal from the center of the bag.
- Meets USP <797> and USP <800> wiper requirements.
- Autoclave safe.
- Individually lot coded for ease of traceability and quality control.

Cleanroom Environment

- ISO Class 5 – 8
- Class 100 – 100,000
- EU Grade B – D

Shelf Life

- Non-Sterile (Dry) – 5 years from date of manufacture

Custom products available upon request.