

Contec



Einweg-Ersatzbezüge EasyReach #MEQT0001

pure¹¹-Nr.: 1110226, Marke: Contec

Eigenschaften

- Marke: Contec
- Breite in cm: 19 cm
- Art des Moppwischbezugs: Flachmopp
- Gewicht in g: 20 g
- Gebrauch: Einweg
- Material: Polyester
- Anzahl in kleinster Unterverpackung: 4
- Polyester/PES: 100 %
- Vorgewaschen

Empfohlene Reinraumklassen

ISO 5|6|7|8|9

GMP C|D

Material

- Polyester

Verpackung

- 60STK

Produktvarianten

pure¹¹-Nr.: 1110226, Einweg-Ersatzbezüge EasyReach #MEQT0001

Passend für Artikel 10321/10322 / VE: 60STK

EasyReach Cleaning Tool

Versatile, lightweight tool for isolators, RABS, UDAFs

The cleaning and disinfection of isolators, Restricted Access Barrier Systems and Unidirectional Airflow Cabinets can often be a difficult task. Designed with operator or product safety in mind, they are not always easy to decontaminate. The **EasyReach Cleaning Tool** was specifically created for this application.

It's rectangular shape makes overlapping straight-line action easy to achieve. A hinged joint along with the ability to lie flat makes this lightweight tool comfortable and easy to use for accessing hard-to-reach areas. The EasyReach Cleaning Tool is available with a choice of fixed or telescoping handles to provide versatility for all sizes of minienvironment.

The 100% laundered polyester pads are designed to yield only a low level of particulates which is essential for use in product contact areas. The single-use, multi-layer cleaning pads are very absorbent, ensuring good even coverage of disinfectant or IPA. The easy grab edge on the cleaning pad ensures the pad fits tightly on the mop frame but is easy to replace with gloved hands.

The unique, presaturated pads make the task of cleaning and disinfecting an Isolator or RABS even easier as no spray bottles need to be passed into the controlled environment, and exactly the same amount of fluid is used by each operator.



EasyReach Cleaning Tool

FEATURES	BENEFITS
Lightweight stainless steel frame and handle	• Suitable for single handed operation, reducing operator fatigue and encouraging compliance. • Autoclavable; can be sterilised by most common methods including gamma irradiation, ethylene oxide, or autoclave (recommended cycle is 121°C for 30 minutes).
Pivoting head with rounded edges and slim profile	• Easy to manoeuvre and ensures even the most awkward areas can be reached while maintaining good contact with the surface. • Ensures there is no possibility of scratching the surface.
Fixed length or telescopic handles	• Short handle 40cm allows transfer into smallest transfer hatches. • Telescoping handles provide versatility for cleaning in large RABS, half suits or incubators minimising the chance of strain through over-reaching.
Rectangular shaped head	• Ideal for correct technique of cleaning and disinfecting with overlapping parallel strokes.
Choice of dry or presaturated 100% 2-ply knitted polyester pads	• Extremely low levels of particles and fibres so suitable for grade A/ISO Class 5 zones. • Provides high level of sorbency for even application of fluids. • Strong and durable with good abrasion resistance. • High level of chemical resistance, compatible with a wide range of disinfectants.
Presaturated with 70% IPA	• Easy to use, ensures the correct amount of solution is used each time by each operator. • Eliminates the need to take bottles into to critical zone.

EasyReach Cleaning Tool



The EasyReach Cleaning Tool is available in two options.

2665LF One-piece stainless steel frame with integrated handle.

2685LF EasyReach Stainless Steel mop head frame with QuickConnect system so can be used with any QuickConnect handle.

The "LF" frame can lay flat to get behind any fitted equipment or hanging rails in the mini-environment.

The EasyReach mop head frame can then be fitted with a choice of dry or presaturated cleaning pads.



2685LF

The most popular handle options are:

2686 One piece stainless steel 40cm

2642 Aluminum extending handle (40cm to 75cm)

2644 Stainless steel extending handle (40cm to 75cm)



2665LF



MEQT0021



MEQT0001



PSME0001-BPR

Part No. Description

EasyReach Cleaning Tool

2665LF	EasyReach Cleaning Tool Lay Flat with integral handle 19 x 6 x 42cm
2685LF	EasyReach Mop Head Frame Lay Flat 19 x 6cm

Mop Heads for EasyReach

MEQT0001	EasyReach 100% Knitted Polyester Cleaning Pads - sewn
MEQT0002SZ	EasyReach 100% Knitted Polyester Cleaning Pads Sterile - sewn
MEQT0021	EasyReach 100% Knitted Polyester Cleaning Pads - ultrasonically sealed
MEQT0022	EasyReach 100% Knitted Polyester Cleaning Pads Sterile - ultrasonically sealed
PSME0001-BPR	EasyReach 100% Knitted Polyester Cleaning Pads presaturated with 70% IPA Sterile - sewn

Mop Handles for EasyReach

2686	QuickConnect Handle Stainless Steel one piece 40cm
2642	QuickConnect Telescopic Handle Anodised Aluminium 40 -75cm
2644	QuickConnect Telescopic Handle Stainless Steel 40 - 75cm

For more information or to request a sample, email infoeu@contecinc.com or phone + 33 (0) 2 97 43 76 98.

EasyReach Cleaning Tool Heads

Product Information

Cover material	100% knitted polyester (PET) 
Cover construction MEQT0021, MEQT0022* MEQT0001, MEQT0002SZ* PSME0001-BPR*	Multi-layer ultrasonically quilted; ultrasonically sealed Multi-layer ultrasonically quilted, sewn Multi-layer ultrasonically quilted; sewn
Saturant	70% IPA (USP Grade) with 30% DI water
Sterility *	Gamma irradiated to a validated SAL 10 ⁻⁶
Shelf life	Sterile: 2 years from manufacturing date
Environment	ISO 4-8 Grade A/B for sterile, C/D for nonsterile
Compatible Mop Frames	2665LF, 2685LF



Technical Information

	MEQT0021 MEQT0022	MEQT0001 MEQT0002SZ	PSME0001-BPR	
Attribute (units)	Typical Value	Typical Value	Typical Value	Test Method
Mop weight, dry; (g)	18.68	20.40	20.40	CTM004-03
Sorbent capacity; (mL/mop)	73	70	N/A	CTM004-03
Particles, P ≥0.5µm; (x10 ⁶ /m ²)	0.24	5.4	3.25	IEST-RP-CC004.2, Sec. 5.1
Fibres > 100µm; (x10 ³ /m ²)	0.01	0.10	0.22	IEST-RP-CC004.2, Sec. 5.2

Packaging Information

Packaging Materials	Low density polyethylene (LDPE) 			
Outer bags (OB1 and OB2)	Corrugated fibreboard (PAP) 			
Case				
	EA/OB1	OB1/OB2	OB2/CS	EA/CS
MEQT0001	4	1	15	60
MEQT0002SZ	4	1	15	60
MEQT0021	4	1	25	100
MEQT0022	4	1	25	100
PSME0001-BPR	8	4	2	64

EA = Each, OB1 = Outer Bag 1, OB2 = Outer Bag 2, CS = Case

Recycling Key

PET	LDPE	PAP
		

Notes

- The data shown are typical values and should not be used as product specifications.
- Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- Current and/or comparison data may be available. Please contact a Contec sales representative for details.
- CTM – Refers to Contec Test Method

EasyReach Cleaning Tool Frames and Handles

Product Information

2665LF EasyReach Cleaning Tool Lay Flat with integral handle
Stainless Steel
19 x 6 x 42cm



2685LF EasyReach Mop Head Frame Lay Flat
Stainless Steel
19 x 6cm



2686 QuickConnect Handle one piece
Stainless Steel
40cm



2644 QuickConnect Telescopic Handle
Stainless Steel
40 - 75cm



2642 QuickConnect Telescopic Handle
Aluminium
40 - 75cm

