



Tuch Vectra Alpha 10

pure¹¹-Nr.: 06005, Hersteller: ITW Texwipe

Zusammenfassung

- Material: Polyester
- Gewicht: 130 g/m²
- Gestrick aus 100% Polyester
- Versiegelte Kanten
- Vorgewaschen
- Lieferform: gelegt

Empfohlene Reinraumklassen

ISO 3 4 5 6 7 8 9

GMP C D

Produktvarianten

pure¹¹-Nr.: 060053131

Farbe: Weiß / Maße: 31 x 31 cm (12 x 12") / Herst.-Nr.: TX1012 / VE: 100 Stück

Quelle: <https://www.pure11.de/tuch-vectra-alpha-10>

Vectra® Alpha® 10 Wipers

Vectra® Process premium polyester sealed-border wipers



Description

Vectra® Alpha® 10 represents the state of the art in wiper technology and provides maximum performance in critical cleanroom environments.

ITW Texwipe's proprietary Vectra® Process cleans the wipers more efficiently than any cleanroom laundry. ITW Texwipe's patented* sealed-border technology produces four fully sealed borders to prevent the release of fibers and particles. The fabric is a no-run interlock, double-knit from 100% continuous-filament polyester.

Alpha® 10 wipers are also available pre-wetted in CleanPaks®. It combines the Alpha® 10 wipers with semiconductor-grade isopropyl alcohol in convenient, reclosable slider bags.

Features

- Excellent balance of wiping efficiency, abrasion resistance and absorbency
- Fully sealed border to prevent fiber release
- Vectra® Process for the cleanest, most consistent wipers
- 100% continuous-filament, double-knit polyester
- Solvent-safe Bag-Within-A-Bag® cleanroom packaging
- Statistical quality control/Six Sigma Quality Assurance

Benefits

- Assures cleanliness with ultralow levels of ions and extractables
- Resists abrasion under rigorous use or when wiping rough surfaces
- Helps prevent product and cleanroom contamination by minimizing fiber and particle release
- Complete traceability of each bag

Applications

- Designed for use in ISO Class 3–5 cleanroom environments
- Ideal for wiping interior of process tools and other equipment
- Superior for general wiping in environments where contamination control is of paramount importance
- The best wiper for multiple applications

Products

TX Number	Dry Wipers	Packaging
TX1010	Vectra® Alpha® 10 9" x 9" nominal (23 cm x 23 cm) double-knit polyester, sealed-border wipers	100 wipers/bag, 2 inner bags of 50; 10 bags/case
TX1012	Alpha® 10 [†] 12" x 12" nominal (31 cm x 31 cm) double-knit polyester, sealed-border wipers	100 wipers/bag, double bagged; 10 bags/case
CleanPaks		
TX8410	AlphaSat® with Vectra® Alpha® 10 9" x 9" nominal (23 cm x 23 cm) wipers pre-wetted with 100%IPA	50 wipers/ reclosable bag 12 bags/case

*Patent #4,888,229

[†]Not Vectra® processed

ITW Texwipe®

North America
1210 South Park Drive
Kernersville, NC 27284
Tel (800) TEXWIPE
(336) 996-7046
Fax (336) 996-2297
www.texwipe.com
info@texwipe.com

Europe/Middle East
Skejby Nordlandsvej 307
DK-8200 Aarhus N
Denmark
Tel +45 87 400 220
Fax +45 87 400 222

Asia/Pacific
50 Tagore Lane
#02-01 Entrepreneur Centre
Singapore 787494
Tel +65 6468 9433
Fax +65 6468 6772

Vectra® Alpha® 10 Wipers

TX1010 TX1046 TX8410

Performance Characteristics

Property	Typical Value	Test Method*
Basis weight	130 g/m ²	1, TM20
Absorbency		
Sorptive capacity	320 mL/m ²	1, TM20
Sorptive rate	0.5 seconds	1, TM20

Contamination Characteristics

Property	Typical Value	Test Method*
LPC		
≥ 0.5 µm	2.9 x 10 ⁶ particles/m ²	1, TM22
Particles and fibers		
Particles 0.5–5.0 µm	1.7 x 10 ⁶ particles/m ²	1, 2, TM22
5.0–100 µm	37,000 particles/m ²	1, 2, TM22
Fibers >100 µm	100 fibers/m ²	1, 2, TM22
Nonvolatile residue		
IPA extractant	0.02 g/m ²	1, TM1
DIW extractant	0.003 g/m ²	1, TM1
Ions		
Sodium	0.04 ppm	1, TM18
Potassium	0.04 ppm	1, TM18
Chloride	0.009 ppm	1, TM18

Note: The data in this table represent typical analyses of these wipers at the time of publication. These are not specifications. ITW Texwipe continually refines both its processes and its products.

*Test Methods

- 1 – “Evaluating Wiping Materials Used in Cleanroom and Other Controlled Environments,” IEST-RP-CC 004.3, Institute for Environmental Sciences and Technology, Rolling Meadows, IL 2004; www.iest.org.
- 2 – “Standard Method for Size-Differentiated Counting of Particles and Fibers Released from Clean Room Wipers Using Optical and Scanning Electron Microscopy,” E2090-00, ASTM International, West Conshohocken, PA, 2000; www.astm.org.
- TM – Refers to ITW Texwipe Test Method — available upon request, contact ITW Texwipe Customer Service at www.texwipe.com for a copy.

ITW Texwipe is the only wiper company to be ISO 9001:2000, 13485:2003, 14001:2004 and OHSAS 18001:1999 registered.